

The design of our models is protected against counterfeiting. ^{TS}

Anti-scratch mittens

Scratch mittens to prevent people from scratching, pulling out catheters or taking off incontinence materials. These are made of a comfortable material and can be washed at 60°C and air-dried.

Quality 1065 : Breathable, moisture-repellent and flame-retardant anti-tear material.

Quality 1010 : Breathable, moisture-repellent and flame-retardant fabric with high tear resistance.



Md 269^{TS}

Anti-scratch mitten with double velcro fastening around the wrist, extra stuffing in the palm of the hand and elastic with safety clasp, per pair.



Washing instructions for quality 1010 and 1065:

1. **Washing** Wash separately at 60°C with little detergent.
2. **Rinse** DO NOT ADD FABRIC CONDITIONER.
3. **Dry** Dry very briefly at low temperature in the dryer or hang to dry.
Do not dry together with moisture-retaining textiles (like cotton,...).