

The design of our models is protected against counterfeiting. <sup>TS</sup>

## Anti-scratch mittens

Scratch mittens to prevent people from scratching, pulling out catheters or taking off incontinence materials. These are made of a comfortable material and can be washed at 60°C and air-dried.

Quality 1065 : Breathable, moisture-repellent and flame-retardant anti-tear material.

Quality 1010 : Breathable, moisture-repellent and flame-retardant fabric with high tear resistance.



### Md 268 C<sup>TS</sup>

Anti-scratch mitten with double velcro fastening around the wrist and extra elastic with safety clasp, per pair.



#### Washing instructions for quality 1010 and 1065:

1. *Washing* Wash separately at 60°C with little detergent.
2. *Rinse* DON'T ADD FABRIC CONDITIONER.
3. *Dry* Dry short at low temperature in the drier or dry hanging.  
Don't dry together with hydrophilic materials (such as cotton,...).