

Anti-scratch mittens

Scratch mittens to prevent people from scratching, pulling out catheters or taking off incontinence materials. These are made of a comfortable material and can be washed at 60°C and air-dried.

Quality 1065 : Breathable, moisture-repellent and flame-retardant anti-tear material.

Quality 1010 : Breathable, moisture-repellent and flame-retardant fabric with high tear resistance.



Md 268 C^{TS}

Anti-scratch mitten with double velcro fastening around the wrist and extra elastic with safety clasp, per pair.



Washing instructions for quality 1010 and 1065:

- 1. Washing** Wash separately at 60°C with little detergent.
- 2. Rinse** DON'T ADD FABRIC CONDITIONER.
- 3. Dry** Dry very briefly at low temperature in the dryer or hang to dry.
Do not dry together with moisture-retaining textiles (like cotton,...).

